Universal-U-Super

75-40



DESCRIPTION:

Ultrasonic Cleaner specifically developed water-dilutable cleaning concentrates for ultrasonic devices. Through a special combination of active cleaning substances, an optimal transmission of sound waves is achieved, resulting in a 100% utilization of the cleaning potential. They are biologically degradable according to EU guidelines. This product does not form stable emulsions with oil-based dirt or wastewater, allowing for easy disposal via approved oil separators in compliance with DIN standards. Local regulations may apply.

USE DIRECTIVES:

Can be diluted with water up to a ratio of 1:40. Non-flammable Safety Instructions: Always follow the safety and hazard warnings on the label. Ingredients:

- <5% anionic surfactants (according to Regulation)
- <5% non-ionic surfactants (EU Regulation 248/2004)

Disposal: Dispose of according to local regulations, refer to the safety data sheet for details.

IDEAL FOR:

- Animal and vegetable fats
- · Oil, proteins, blood
- Waxes, flux agents
- Pastes, soot, and bitumen
- Resins and crusts
- Adhesives
- Lead and felt-tip pen markings
- Rubber residues and rubber abrasion





Content	Туре	ArtNo	
960 ml [32.46 fl.oz.]	sprayer	75-4001	12
4 l [1.06 gal.]	canister	75-4004	4
20 l [5.28 gal.]	canister	75-4020	1



